



Ohaus AX4202N-E Adventurer AX Precision Balance (30122655) with External Calibration 4200 x 0.01 g and Legal for Trade 4200 x 0.1 g

Striking the ideal balance between inventive features and functional, uncomplicated weighing capabilities, the OHAUS Adventurer incorporates all of the applications necessary for routine weighing and measurement activities.



Capacity x Readability
Non Legal Mode: 4200 g x
0.01 g
Legal For Trade: 4200 g x 0.1
g

Pan Size
6.9 x 7.7 in (Diameter)

Manufacture: Ohaus
SKU: AX4202N-E
UPC: B01BTXVKS2
Weight: 20.00 lb
Free Ground Shipping within the
48 continental US States



Legal for Trade

Please Call
(800)832-0055

Features

The Most Complete Balance in its Class Striking the ideal balance between inventive features and functional, uncomplicated weighing capabilities, the OHAUS Adventurer incorporates all of the applications necessary for routine weighing and measurement activities. With a color touchscreen, GLP/GMP compliance capabilities, two USB ports, ingenious draftshield, and much more, Adventurer is the most complete balance in its class

Standard Features Include:

- Stability, Accuracy, and Fast Operation Ensure Optimal Weighing Results — This trio of characteristics ensures the most important aspects of routine laboratory weighing are covered: accurate results you can count on extremely quickly.
- Color Touchscreen & Connectivity Options Power a Modern Weighing Experience — The wide viewing angle color touchscreen provides quick access to all of Adventurer's applications, while dual USB ports with GLP/GMP tracking capabilities assist in the monitoring and reporting of data.
- Space-saving Draftshield Improves User Experience and Accessibility — The two piece, top-mounted draftshield doors open wide on both sides, providing ample room for sample placement, and also reduce the footprint of the draftshield in the rear of the balance when open.

Stability, Accuracy, and Fast Operation Ensure Optimal Weighing Results in Routine Weighing Tasks

Weighing Performance

- Delivers stable and reliable weighing results for routine weighing tasks Stabilization Time
- Adventurer's fast stabilization time improves productivity in the laboratory Calibration
- External Calibration — Traditional calibration in which the operator manually calibrates the balance with their choice of calibration weight value to ensure accuracy available on every model.
- AutoCal™ — Select models feature OHAUS' automatic internal calibration system that performs routine maintenance by calibrating the balance daily.

Color Touchscreen Offers Easy and Fast Operation of Adventurer's Applications

- Operate and access Adventurer's nine application modes and abundant features that eliminate the need to do several manual calculations through the modern color touchscreen
- Operators can wear laboratory gloves while utilizing the touchscreen, eliminating the inconvenience and hazards associated with constantly putting on and removing gloves
- In addition to the touchscreen, Adventurer also has six mechanical keys that provide tactile feedback and allow the operator to perform repetitive operations such as tare, zero, calibration, and print
- **Application Modes**
- **Weighing** - Determine the weight of items in the selected unit of measure.
- **Dynamic Weighing** - Weigh an unstable load. Scale takes an average of weights over a period of time
- **Display Hold** - Manually holds the last stable weight or highest weighing value on the display.
- **Parts Counting** - Count samples of uniform weight.
- **Density Determination** - Determine density of solids or liquid. With the weigh below hook, it's possible to perform specific gravity tests for objects that cannot be easily placed on the weighing pan.
- **Totalization** - Measure cumulative weight of multiple items. Cumulative total may exceed balance capacity.
- **Percent Weighing** - Measure the weight of a sample displayed as a percentage of a preestablished Reference Weight.
- **Check Weighing** - Compare the weight of a sample against target limits.
- **Formulation** - For compounding and recipe making. The number of components can range from 2 to 50.

Equipped with the Connectivity and Functional Features Required in Laboratories

Dual USB Ports

- A front USB host port is easily accessible and makes it simple to load data from the balance on to a flash drive without having to reach around to the back or move the balance
- A second USB device is located at the rear of the balance that can be used to connect the balance to a PC
- The connectivity options help meet traceability requirements in traditional installations

Real Time Clock with GLP/GMP Data

- A real-time clock function keeps accurate time even during power loss and the GLP data capability has the ability to record Sample name, Project names and Balance ID's to help meet traceability and compliance requirements

Balance Profiles

- The cloning feature allows you to save user and application settings to a USB flash drive which can be easily used to configure additional Adventurer balances

Below Minimum Sample Weight Indication

- When using the minimum weight feature, the display clearly indicates that your current sample weight is below your

Space-saving Draftshield Designed to Improve User Experience and Accessibility

- Draftshield doors are constructed of two glass panels, reducing the space required on the lab bench when the doors are open
- Wide door entry provides unobstructed access and allows larger weighing vessels to be easily placed on the pan, reducing the chance of accidental spillage
- Easy to keep clean in order to ensure a safe workspace by minimizing contamination

Specifications

Standard Models with Internal Calibration	AX124	AX224	AX324	AX223	AX423	AX523	AX622	AX1502	AX2202	AX4202	AX5202	AX4201	AX8201
Models with External Calibration	AX124/E	AX224/E	-	AX223/E	AX423/E	AX523/E	AX622/E	AX1502/E	AX2202/E	AX4202/E	-	AX4201/E	AX8201/E
Capacity x Readability (g)	120 x 0.0001	220 x 0.0001	320 x 0.0001	220 x 0.001	420 x 0.001	520 x 0.001	620 x 0.01	1520 x 0.01	2200 x 0.01	4200 x 0.01	5200 x 0.01	4200 x 0.1	8200 x 0.1
Repeatability std (g)	±0.0001			±0.001			±0.01			±0.1			
Weighing Units	gram, milligram, mesgal, momme, Newton, ounce, pennyweight, Baht, carat, grain, pound, Tael (Hong Kong), Tael, (Singapore), Tael (Taiwan), tical, tola, troy ounce, custom (1)												
Legal For Trade with Internal Calibration	-	AX224N	-	-	AX423N	-	-	-	-	-	-	-	-
Legal For Trade Models with External Calibration	-	-	-	AX223N/E	AX423N/E	AX523N/E	AX622N/E	AX1502N/E	AX2202N/E	AX4202N/E	-	-	AX8201N/E
Legal For Trade Capacity x Readability (g)	-	220 x 0.001	-	220 x 0.01	420 x 0.01	520 x 0.01	620 x 0.1	1520 x 0.1	2200 x 0.1	4200 x 0.1	-	-	8200 x 1
Class	-	I	-	II			II			-			II
Legal For Trade Weighing Units	-	lct, grain, g, mg, oz, ozt, dwt	-	ct, grain, g, mg, oz, ozt, dwt, kg			ct, grain, g, oz, ozt, dwt, lb, kg			-			ct, grain, g, oz, ozt, dwt, lb, kg
Legal For Trade Approvals	-	NIST, Measurement Canada	-	NIST, Measurement Canada			NIST, Measurement Canada			-			NIST, Measurement Canada
Typical Operating Range (g) (u=0.10%, k=2)	0.20g - 120g	0.20g - 220g	0.20g - 320g	2.0g - 220g	2.0g - 420g	2.0g - 520g	20.0g - 620g	20.0g - 1,520g	20.0g - 2,200g	20.0g - 4,200g	20.0g - 5,200g	200.0g - 4,200g	200.0g - 8,200g
Optimal Operating Range (g) (u=0.10%, k=2)	0.082g - 120g	0.082g - 220g	0.082g - 320g	0.82g - 220g	0.82g - 420g	0.82g - 520g	8.2g - 620g	8.2g - 1,520g	8.2g - 2,200g	8.2g - 4,200g	8.2g - 5,200g	82g - 4,200g	82g - 8,200g
Sensitivity Drift (ppm/°C)	1.5			3			3			1.9	9		
Linearity (g)	±0.0002			±0.002			±0.02			±0.2			
Stabilization Time (sec)	≤3			≤2			≤1.5			≤1.5			
Pan Size	Ø 3.5 in / 90 mm			Ø 5.1 in / 130 mm			6.9 x 7.7 in / 175 x 195 mm						
Tare Range	To capacity by subtraction												
Power Requirements	AC Adapter Input: 100-240 VAC 0.3A 50-60 Hz AC Adapter Output: 12 VDC 0.84A												
Display Type	Full-Color Touchscreen WQVGA Graphic LCD												
Display Size	4.3 in / 109 mm (diagonal)												
Base Housing (W×H×D)	13.93 x 13.39 x 9.05 in / 354 x 340 x 230 mm						13.93 x 3.94 x 9.05 in / 354 x 100 x 230 mm						
Communication	RS232, USB Device, USB Host												
Temperature Range	50°F to 86°F/10°C to 30°C												

Humidity Range	Maximum relative humidity 80 % for temperatures up to 86°F/30°C
Storage Conditions	14°F/-10°C to 140°F/60°C at 10% to 90% relative humidity, non-condensing
Shipping Dimensions	20.0 × 15.4 × 20.9 in / 507 × 387 × 531 mm

22.0 × 15.5 × 11.9 in / 557 × 392 × 301 mm

Additional Features RS232 interface, integral weigh below hook, full housing in-use cover, removable stainless steel pan, die-cast metal bottom housing, security bracket, illuminated up-front level indicator, four adjustable feet, software lockout menus, stability indicator, software overload/underload indicators, user selectable environmental settings, audible indicator, user selectable brightness settings, auto dim, touchscreen calibration, auto tare, user selectable operating language (nine)

Approvals Metrology: NIST Handbook 44, Measurement Canada Weights and Measures Regulations (Class I, nmax 220000; Class II, nmax 52000) Product Safety: CSA C22.2 No. 61010-1, UL 61010-1, IEC 61010-1 Electromagnetic Compatibility: FCC Part 15 Class A, ICES-001 Class A, IEC 61326-1 (emissions Class B, immunity Industrial requirements)

i81u812

[Contact US](#)

[718-336-5900](#)

[Returns](#)

[Store Policies](#)

[About Us](#)

- Phone: [\(800\)832-0055](#) or [\(718\)336-5900](#)
- Chat with us via [WhatsApp Chat](#)
- Address: 4802 Glenwood Rd. Brooklyn, NY 11234
- © 2000 - 2020 scalesgalore.com (a division of Itin Scale Co., Inc.) All rights reserved.