ITIN SCALE COMPANY

Full featured precision weighing scale with a range of features. 7 Built-in application modes plus below balance weighing: animal weighing, parts counting, percent weighing, check weighing, filling and gross/net/tare

Ohaus EP4101 Explorer Pro Precision Balance, 4100 g x 0.1 g





Manufature: Ohaus **SKU: EP4101** Weight: 30.00 lb Free Ground Shipping within the 48 continental US States

> **Please Call** (800)832-0055

> > in-use cover

Features

Ohaus Explorer lab scales have multiple weighing modes, auto zero tracking, RS232, GLP, auto tare. Custom LCD with 7 characters, four user-friendly applications and more. Capacity x precision: 4100 g x 0.1 g

The Explorer Pro Series of standard level balances was designed for simplicity and includes the industry's easiest user interface for easy setup and operation; no training is required. The Explorer Pro offers all the features and durability found in high-end laboratory balances plus the traditional Ohaus quality and support for years of trouble free use!

- Simple 2 key menu operation and navigation

Ready to weigh without complicated setup Innovative man-machine interface and user promps make Explorer Pros advanced applications easy to follow and easy to use Three soft keys are application specific allowing direct access to items such as calibration, units, new sample, sample size, new reference weight, reference weight, new target and/or therease

- Innovative man-machine interface and user promps make Explorer Pros advanced applications easy to follow and easy to use
 There soft keys are application specific allowing direct access to items such as calibration, units, new sample, sample size, new reference weight, reference weight, new target and/or target.
 Flexibility to display either simple weighing results or more advanced results including piece count, average piece weight, sample size, tare weight, weight, under and over indicators Selectable operating languages including English, Spanish, Italian, French and German
 7 Built-in application modes plus below balance weighing: animal weighing, parts counting, percent weighing, check weighing, filling and gross/net/tare
 Only Explorer Pros applications and dot matrix display allow for simultaneous viewing of reference information including piece count, percent, under/over/accept and actual weight
 Parts counting also includes parts counting check and parts counting fill functions
 Parts counting also includes parts counting check and parts counting fill functions
 Parts counting also includes parts counting the relationship between the total load on the platform and a target
 Gross/net/tare application with fill guide displaying the relationship between the total platform load and the full balance capacity
 Brilliant backlit high resolution do displays (display in the relationship between the total platform load and a user difficed target
 Grapcity guide provides a visual aid by displaying the relationship between the total platform load and a user difficed target
 Grapcity guide provides a visual aid by displaying the relationship between the total platform load and a user difficed target
 Grapcity guide provides a visual aid by displaying the relationship between the total platform load and a user difficed target
 Grandard RS2322 port

Models without AutoCal™:	EP213	EP413	EP413D	EP613	EP612	EP2102	EP4102	EP4102D	EP6102	EP4101	EP6101	EP8101	EP12001	EP22001	EP3200
Models with AutoCal™:	EP213C	EP413C	EP413DC	EP613C	EP612C	EP2102C	EP4102C	EP4102DC	EP6102C	EP4101C	EP6101C	EP8101C	EP12001C	EP22001C	EP32001
Capacity (*draft shield included)	*210 g	*410 g	*100/410 g	*610	610 g	2100 g	4100 g	1000/4100g	6100	4100 g	6100 g	8100 g	12000	22000	32000
Readability (g)	0.001		0.001/0.01	0.001	0.01	0.01	0.01	0.01/0.1	0.01 g				0.1		
Repeatability (std dev) (g)	0.0005		0.0005 / 0.005		0.0005			0.01/0.05	0.005	0.05			0.1		
Linearity (g)	± 0.002 g		± 0.002 / 0.005	±0.002	±0.02		±0.02 / 0.05	±0.04	±0.1			±0.4			
Weighing Modes	gram, kilogram, pound, ounce, troy ounce, carat, pennyweight, Hong Kong Tael, Singapore Tael, Taiwan Tael, mommes, grain, tical, Newton, custom														
Application Modes	weighing, parts counting, animal/dynamic weighing, checkweighing, percent weighing, filling, gross/net/tare weighing differential weighing, formulation quick check, statistics														
Features	RS232 port, auxiliary display port, GLP protocol, selectable language display text, selectable displayed information settings, selectable environmental filters, selectable auto-print settings, integral weigh below hook, contrast & brightness control, protective in-use cover									port, GLP enviror selectable weigh bel	port, auxiliary display P protocol, selectable onmental settings, ile auto-print settings, elow hook, contrast & ess control, protective				

Tare Range	full capacity by subtraction									
Stabilization Time		4 seconds								
Operating Temperature	50° to 86°F / 10° to 30° C without internal calibration / 50° to 104°F / 10° to 40° C with internal calibration									
Calibration	External / Internal									
Display	High Resolution LCD Dot Matrix with back light									
Power Requirements	100-120 V ac, 220-240 V ac, 50/60 Hz									
Pan Size (in/cm)	4.7" (12 cm) diameter	6.8" x 6.8" (17.2 x 17.2 cm) with windshield	8" x 8" (20.3 x 20.3 cm)	11" x 14" (28 x 35.6 cm) av						
Dimensions (W x H x D)	8.3" x 13.8" x 13.8" (21 x 35 x 35 cm)	14" x 5.5 " x 17.5" (36 x 14 x 44.5 cm)								
Net Weight	13.2 lb (6 kg)	27 lb (12.3 kg)								
Туре		Explorer Pro High Capacity								

i81u812



Phone: (800)832-0055 or (718)336-5900 Chat with us via <u>WhatsApp Chat</u> Address: 4802 Glenwood Rd. Brooklyn, NY 11234 © 2000 - 2023 scalesgalore.com (a division of Itin Scale Co., Inc.) All rights reserved.